

Dia

Thermal Cameras

DiaCAm Cameras: Affordable Thermographic Diagnostics

- Compact and lightweight: ergonomics designed for effortless handling
- Particularly easy to use
- Excellent thermal sensitivity: 0.08°C
- Wide dynamic range for measurement (-20°C to +250°C)



Thermal Cameras

BUILDING DIAGNOSTIGS

To improve comfort or optimize a building's energy performance, thermal cameras are **powerful tools capable of detecting faults and irregularities** related to thermal bridges, thermal insulation, airtightness or problems involving water.



• Detection of insulation faults, air leaks, thermal bridges and excessive humidity.

Dia

• Detection of leaks, blockages and embedded ducts.



Industrial maintenance and repair

These thermal cameras are ideal for electrical maintenance, highlighting any electrical equipment malfunctions and particularly abnormal overheating.



- overloads
- unbalances
- Faulty electrical contacts

Mechanical and electrical applications

To detect anomalies or malfunctions on internal components in order to prevent motor overheating, the **DiaCAms** are simple, effective tools for quick diagnostics.



The **DiaCAms** can be used to check and test mechanical parts and assemblies: areas of wear, incorrect shaft alignment, lubrication problems, etc.

The advantages of the C.A 1882

With its wide-angle lens, the C.A 1882 is ideal for detecting energy losses when inspecting buildings.

It is also equipped with the MixVision function which allows you to link a thermogram to a real image.

This function enables you to define how much of the infrared image is merged with

the real image, using a scale from 0 to 100 %.

Dia

Advantages



Thermal sensitivity

The greater the thermal sensitivity, the easier it is to view small temperature differences, providing users

with more detailed images. This specification is crucial, and particularly for building thermography, where some faults cause small temperature differences (e.g. insulation faults).



Dynamic range for measurement

The **DiaCAms** offer a wide measurement range. The dynamic ranges for the targets may vary from -20 °C to +250 °C.



Recording Up to 1,000 therma

Up to 1,000 thermal images on SD cards as a standard feature.



Integrated functions

A wide range of integrated tools, manual cursors, automatic detection of hot or cold points, alarms.



Preview and analysis Software

The **DiaCAm Preview** software is ideal for analysing infrared images. Its easy-to-use interface means quick access for everyone. In addition, all the analysis functions are already integrated in the toolbar.

- Cursors (automatic display of the temperature at the chosen point).
- Thermal profile (automatic display of Min/Max/Avg on the line).
- A square or circle for analysis by zone (ideal for comparing Min/Max/Avg between terminals, for example).
- Charts of results automatically and very quickly show all the information/analytical tools on the thermogram.
- "Max" function automatically indicates the hot point in the thermogram or in a predefined area for analysis.
- Polygons and polylines for more detailed analysis of certain areas in the thermogram.



Technical Specifications

	C.A 1877	C.A 1878	C.A 1882		
Detector specifications					
Detector	80 x 60	100 x 80	160 x 120		
Туре		UFPA microbolometer, 8-14 µm			
Frequency	9 Hz		50 Hz*		
Sensitivity (N.E.T.D)	0.08 °C @ 30 °C				
	Temperature measurement				
Temperature range	-20 °C to +250 °C				
Accuracy	\pm 2 °C or \pm 2 % of reading				
Image performance					
Thermal image					
Field of view	10° x 8°	12° x 10°	38° x 28°		
Spatial resolution	2.2	mrad	4.4 mrad		
Min. focal distance		10 cm			
Focusing	Manual				
Real image	No		Yes		
"MixVision" mode		-	Merge function with adjustment from 0 to 100 % of the level of the thermal image overlay in the real image		
Image size	- 640 x 480 pixels		640 x 480 pixels		
		Functions			
Emissivity correction	Yes				
Parameter settings	Emissivity, environmental temperature, distance, relative humidity				
Measurement tools	1 manual cursor + automatic Min/Max detection on adjustable area + adjustable alarm (C.A 1877 & C.A 1878)				
Laser pointer	Yes				
Memory	1,000 thermal images as standard				
Type of storage	Removable 2 GB SD card (as standard), up to 16 GB				
Screen	2.5 inches, multi-directional				
	Gen	neral specifications			
Battery	Lithium-Ion rechargeable battery / Battery life: 3 hours				
Battery recharging	Recharging via external charger				
Protection	IP54				

* 9 Hz outside the European Union

References to order

C.A	1877 IR thermal camera	P01651277
C.A	1878 IR thermal camera	P01651278
C.A	1882 IR thermal camera	P01651215
C.A	1882 9 Hz IR thermal camera	P01651215E

Accessories

Battery	. P01296045
Battery charger	. P01296046
Bag	. P01298075
Docking station	. P01651528
Mains power supply	. P01651527
Sun-shade	. P01651532
In-vehicle charger adapter	. HX0061
C.A 1875 training bench	. P01651620

Standard states at delivery:

C.A 1877 or C.A 1878: delivered in plain cardboard box with battery charger, battery, 2 GB SD card, SD card reader, DiaCAm Preview software on CD-ROM, operating manuals and measurement reports.

C.A 1882: delivered in plain cardboard box with battery charger, docking station, battery, 2 GB mini-SD card, SD card reader, video cable, RayCam Preview software on CD-ROM, operating manuals and measurement reports.



For assistance and ordering

FRANCE

Chauvin Arnoux 190, rue Championnet 75876 PARIS Cedex 18 Tel: +33 1 44 85 44 38 Fax: +33 1 46 27 95 59 export@chauvin-arnoux.fr www.chauvin-arnoux.fr

UNITED KINGDOM

Chauvin Arnoux Ltd Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk Dewsbury, West Yorkshire - WF12 7TH Tel: +44 1924 460 494 Fax: +44 1924 455 328 info@chauvin-arnoux.co.uk www.chauvin-arnoux.com

MIDDLE EAST **Chauvin Arnoux Middle East** P.O. BOX 60-154 1241 2020 JAL EL DIB - LEBANON Tel: +961 1 890 425 Fax: +961 1 890 424 camie@chauvin-arnoux.com www.chauvin-arnoux.com

